Adjustable Tension Levers

24440.0602



Product Description

Material

Lever

· Stainless steel 1.4305, dull blasted

Inner parts

• Stainless steel 1.4305, dull blasted

Ball knob

· Thermosetting plastic PF 31, black, DIN 319

Operation


By lifting the lever the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.


More information


Notes

The threaded portion can be exchanged.

Drawing







Order information

Dimensions										I	Art. No.
d ₁	d ₂	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	ı	t	_	
								~	min.		
[mm]										[g]	
with female thread – picture 1, Stainless steel											
21	M8	13.5	8	20	33.5	4	1	70	11	89	24440.0602

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1
Published on: 10.8.2024