# Adjustable Flat Tension Levers • with screw 24441.0905



#### **Product Description**

Adjustable flat tension levers are used when the swivel range is limited or a specific lever position is required.

Adjustable flat tension levers are characterised by their low construction height and are particularly suitable for use in restricted spaces or when the lever should not overhang.

#### **Material**

#### Lever

 Zinc die-cast, plastic coated, silver, similar to RAL 9006, matt structure

# • Steel blac

Steel, blackened

#### Screw

Steel, blackened


#### Covering


· Plastic, light grey

#### Operation

**By lifting the lever** the serrations are disengaged. The lever can be positioned by the serrations. On releasing the lever, the serrations are automatically re-engaged.

# Drawing









#### **Order information**

Dimensions									ß		Ĭ	Art. No.
d1	d <sub>2</sub>	l <sub>1</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	I <sub>2</sub>	min.	max.		
	[mm]								[°C]			
				[mm]					D°]	]	[9]	
silver				[mm]					O°]	]	[9]	

### **Application example**





## Compliance

**RoHS compliant** Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

#### **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.