High Knurled Nuts • DIN 466 24780.0300



Product Description

Knurled nuts are very versatile. Three material versions for the different requirements

- Steel, blackened
- · Steel, zinc-plated by galvanization
- Stainless steel
- are available.

Knurled nuts can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers. The high knurled nuts are manufactured according to DIN 467.

Material

• Stainless steel 1.4305, dull blasted

More information


Notes

Knurling pitch and knurling depth may differ from DIN.

Further products

• Flat Knurled Nuts, DIN 467


Drawing



Order information

Dimensions					X	Art. No.
d ₁	d ₂	d ₃	h	k	-	
	[mm]					
Stainless steel						
M10	36	20	23	8	85	24780.0300

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.