# Hinges • adjustable 25161.0225



# **Product Description**

Adjustable hinges can be positioned horizontally or vertically by moving the adjusting bushings in a form-fit and finely adjusted manner.

#### Material


# Body


Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure


#### Axis


· Stainless Steel

# **Drawing**























# **Order information**

Dimensions											I	Art. No.	
<b>b</b> <sub>1</sub>	I <sub>1</sub>	b <sub>2</sub>	<b>b</b> <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>2</sub>	x			
	[mm]										[g]		
adjustabl	adjustable in height – picture 2, Zinc die-cast, black												
50	64	37	28	5.5	6	11.5	7	6.5	27	0.75	142	25161.0225	

Page 1 of 2 www.halder.com Published on: 10.8.2024

## Compliance

## **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024