Hinges · adjustable

25161.0230



Product Description

Adjustable hinges can be positioned horizontally or vertically by moving the adjusting bushings in a form-fit and finely adjusted manner.

Material


Body


 Zinc die-cast, plastic coated, black, similar to RAL 9005, matt structure


Axis


· Stainless Steel

Drawing






















Order information

Dimensions											I	Art. No.
b ₁	l ₁	b ₂	b ₃	d₁	d ₂	h ₁	h ₂	h ₃	l ₂	x		
	[mm]										[g]	
adjustable in height – picture 2, Zinc die-cast, black												
60	76	42	33.5	6.5	8	15	9	8.5	34	1	257	25161.0230

www.halder.com Page 1 of 2
Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 10.8.2024