# **SIMPLEX sledge hammers** • TPE-soft / TPE-mid; with cast iron housing and Hickory handle 3013.081





#### **Product Description**

The SIMPLEX series 3013 is available with the insert combination of TPE-soft / TPE-mid. Both inserts are thermoplastic elastomers and do not leave behind any colour marring or - unlike a conventional rubber mallet - any undesired black marring.

The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch.

The grey, medium hard TPE-mid insert (series 3203) allows for a more powerful impact force that is comparable to that of the rubber composition insert (series 3202).

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

Measuring 3,125g and 80cm in total weight and total length, respectively, this sledge hammer is available in D80mm.

Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, no marring) / TPEmid (grey, medium hard, no marring).
- · Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in D80mm (3,125g total weight).

#### **Application Areas**

Gardening and landscaping, natural stone setting, drywall construction, furniture assembly, and joiner's work

#### **Material**

#### Handle

Hickory

#### insert 1

- TPE-soft, blue
- Non-marring
- Soft

#### insert 2

- TPE-mid, grey
- Non-marring
- Medium hard

## Housing

· Cast iron

## **Order information**

Dimensions				Ĭ	GTIN		ecl@ss 10.1	Art. No.
Ø		-	Length x Width x Height			5.0		
[mm]				[g]				
80	175	800	800 x 175 x 80	3125	4030618312369	AAA938c002	21-04-09-20	3013.081

# Compliance

# **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

# Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.