Clamps • stepped EH 23160.




Product Description

This clamp (clamping claw) according to DIN 6314 B is stepped and is mainly used in mechanical clamping technology for clamping workpieces.

Material

· Heat-treated steel, tempered, blackened

Drawing




Order information

Nominal	Dimensions											For screws		I	Art. No.
dimension b ₁	ı	а	b ₂	b ₃	С	e ₁	e ₂	e ₃	h	h ₁	h ₂				
[mm]	[mm]											[mm]	[in]	[g]	
6.6	55	8	15	8	5	11	15.5	36	16	11	2	M 6	1/4	39	23160.0107
9.0	70	10	20	10	8	15	19.5	46	20	14	3	M 8	5/16	80	23160.0109
11.0	90	13	25	12	10	19	26.5	58	25	18	4	M10	3/8	168	23160.0111
13.0	115	16	30	15	12	24	32.5	75	32	23	5	M12	1/2	325	23160.0113
17.0	145	20	40	20	14	29	38.5	99	40	28	6	M16	5/8	685	23160.0117



Page 1 of 2 Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024