# Clamping Elements EH 23700.



# **Product Description**

#### Material

#### Body

· Steel, blackened

Wearing parts
• Heat-treated steel

#### Pull-rod


· Special steel


#### More information

#### **Further products**

- Straight Clamps, long
- Intermediate Elements
  Intermediate Elements, with support
- Base Elements
- Base Elements, swivelling
- Base Elements, low
- · Base Elements, for location hole

## Drawing





# **Order information**


Dimensions												I	Art. No.
а	b	С	b <sub>1</sub>	е	f	g	h <sub>1</sub>	h <sub>2</sub>	i	ı	n	_	
[mm]												[g]	
25	25	65	35	110	20	M12	48 – 78	112	12.5	40	10	870	23700.0012
30	30	78	40	142	30	M16	60 – 96	145	14.0	50	13	1703	23700.0016



Erwin Halder KG

Page 1 of 2 www.halder.com Published on: 10.8.2024

## **Application example**



#### Compliance

#### **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### **Does not contain SVHC substances**

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024