

## Star Grips • DIN 6336 grey cast iron EH 24650.



### Product Description

These star grips are manufactured according to DIN 6336. Sandblasted or tumbled.

### Material

#### Handle


- Grey cast iron GG 20, bright

### More information


#### Notes

Grips with different bores or surface treatment can be obtained on request.


### Drawing





picture 1




picture 2



picture 3




picture 4



picture 5

### Order information

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	Dimensions						[g]	Art. No.
				d <sub>5</sub> [mm]	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	t <sub>1</sub> min.	t <sub>2</sub>		
<b>raw part, form A – picture 1</b>											
32	12	–	–	–	21	–	10	–	–	55	24650.0032
40	14	–	–	–	26	–	13	–	–	77	24650.0040
50	18	–	–	–	34	–	17	–	–	147	24650.0050
63	20	–	–	–	42	–	21	–	–	314	24650.0063
80	25	–	–	–	52	–	25	–	–	629	24650.0080
<b>with smooth throughgoing bore, form B – picture 2</b>											
32	12	6	–	–	–	20	–	–	–	186	24650.0132
40	14	8	–	–	–	25	–	–	–	72	24650.0140
50	18	10	–	–	–	32	–	–	–	130	24650.0150
63	20	12	–	–	–	40	–	–	–	275	24650.0163
80	25	16	–	–	–	50	–	–	–	548	24650.0180
<b>with smooth blind hole, form C – picture 3</b>											
32	12	6	–	–	–	20	–	12	–	40	24650.0232
40	14	8	–	–	–	25	–	15	–	74	24650.0240
50	18	10	–	–	–	32	–	18	–	133	24650.0250
63	20	12	–	–	–	40	–	22	–	280	24650.0263
80	25	16	–	–	–	50	–	28	–	573	24650.0280
<b>with thread, drilled out, form D – picture 4</b>											
32	12	–	M 6	6.4	–	20	–	–	10	39	24650.0332
40	14	–	M 8	8.4	–	25	–	–	13	72	24650.0340
50	18	–	M10	10.5	–	32	–	–	16	125	24650.0350
63	20	–	M12	13.0	–	40	–	–	20	277	24650.0363
80	25	–	M16	17.0	–	50	–	–	20	541	24650.0380

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	Dimensions							Art. No.
				d <sub>5</sub> [mm]	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	t <sub>1</sub> min.	t <sub>2</sub>		
<b>with threaded blind hole, form E – picture 5</b>											
32	12	–	M 6	–	–	20	–	12	–	40	<a href="#">24650.0432</a>
40	14	–	M 8	–	–	25	–	15	–	186	<a href="#">24650.0440</a>
50	18	–	M10	–	–	32	–	18	–	132	<a href="#">24650.0450</a>
63	20	–	M12	–	–	40	–	22	–	280	<a href="#">24650.0463</a>
80	25	–	M16	–	–	50	–	28	–	572	<a href="#">24650.0480</a>

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.