# **SIMPLEX soft-face mallets** • TPE-soft / nylon; with aluminium housing and high-quality wooden handle

EH 3118.





### **Product Description**

The SIMPLEX series 3118 is available with the insert combination of TPE-soft / nylon. The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is composed of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. Moreover, it is also oil and grease resistant.

The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D60mm.

#### Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, no marring) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily
  apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- · Available in sizes of D30mm to D60mm.

#### **Application Areas**

Folding and bending work, positioning and adjusting of light/delicate workpieces , joiner's work, furniture assembly, tinsmith work

## Material

## Handle

Wood

## insert 1

- · TPE-soft, blue
- · Non-marring
- Soft

## insert 2

- · Nylon, white
- hárd
- Very wear-resistant
- no chipping (even at tempeatures below zero)
- · Oil and grease resistant

#### Housing

Erwin Halder KG

Aluminium Al

## **Order information**

Dimensions				I	GTIN	proficl@ss	ecl@ss 10.1	Art. No.
Ø	<b>—</b> i;	<b>=</b>	Length x Width x Height	_		5.0		
[mm]			[9]					
30	90	295	295 x 90 x 30	205	4030618305279	AAA905c002	21-04-09-16	3118.030
40	115	325	325 x 115 x 40	380	4030618305286	AAA905c002	21-04-09-16	3118.040
50	135	370	370 x 135 x 50	670	4030618305293	AAA905c002	21-04-09-16	3118.050
60	150	405	405 x 150 x 60	875	4030618305309	AAA905c002	21-04-09-16	3118.060



www.halder.com Page 1 of 2

Published on: 10.8.2024

# **Application example**



# Compliance

## **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## **Does not contain SVHC substances**

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

# **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024