

## SIMPLEX soft-face mallets • TPE-mid / plastic; with aluminium housing and high-quality wooden handle EH 3136.



### Product Description

The SIMPLEX series 3136 is available with the insert combination of TPE-mid / plastic. The grey TPE-mid insert (series 3203) allows for an impact force that is comparable to the black rubber insert. The difference is that it will not leave any undesired black marring. The red plastic insert (series 3206) is hard and also oil and grease resistant. The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D60mm.

#### Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-mid (grey, medium hard, no marring) / plastic (red, hard, oil and grease resistant).
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

### Application Areas

Versatile use, assembly and repair work, maintenance work, sheet-metal forming, prefabricated house construction, carpenter's work, scaffold construction, tent construction

### Material

#### Handle

- Wood

#### insert 1

- TPE-mid, grey
- Medium hard
- Non-marring

#### insert 2

- Plastic, red
- hard
- Oil and grease resistant
- Universal

#### Housing

- Aluminium Al

### Order information

Ø	Dimensions		Length x Width x Height [mm]	[g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
30	90	295	295 x 90 x 30	202	4030618305392	AAA905c002	21-04-09-16	3136.030
40	115	325	325 x 115 x 40	375	4030618305408	AAA905c002	21-04-09-16	3136.040
50	135	370	370 x 135 x 50	660	4030618305415	AAA905c002	21-04-09-16	3136.050
60	150	405	405 x 150 x 60	875	4030618305422	AAA905c002	21-04-09-16	3136.060

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.