SIMPLEX soft-face mallets • Copper; with reinforced cast iron housing and fibre-glass handle EH 3704.





Product Description

The SIMPLEX series 3704 is equipped with copper inserts on either side. Representing the hardest insert in the SIMPLEX selection, this insert (series 3804) produces extremely high impact forces but in a way that is gentler compared to a steel hammer. It is the replacement for a conventional copper hammer.

The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force.

Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture).

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes D30mm and D40mm.

Product features:

- SIMPLEX soft-face mallet with copper inserts (hard) on both sides
- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- · All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in D30mm and D40mm.
- · Replaces classic copper hammers.

Application Areas

For very high impact, straightening work, plant construction, sheet-metal working, assembly, repair and maintenance work

Material

Handle

· Fibreglass with rubber grip

Inserts

- Copper with plastic socket
- hard

Housing

Reinforced cast iron, black


Assembly

Copper inserts must only be mounted into reinforced cast iron housings!

Order information

Dimensions				I	GTIN	proficl@ss	ecl@ss 10.1	Art. No.
ø		i	Length x Width x Height	-		5.0		
[mm]								
			[mm]	[g]				
30	90	300	[mm] 300 x 90 x 34	[g] 690	4030618300786	AAA905c002	21-04-09-16	3704.030

Application example





Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.