SIMPLEX soft-face mallets • Plastic / nylon; with reinforced cast iron housing and fibre-glass handle

EH 3768.





Product Description

The SIMPLEX series 3768 comes with the insert combination of plastic / nylon. The red plastic insert (series 3206) is hard and also oil and grease resistant. The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. Composed of extruded and extremely homogeneous material, it is considerably more wear-resistant and durable and will not chip even at temperatures below zero. Moreover, it is also oil and grease resistant. The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall

thicknesses and struts. The increase in weight ensures greater impact force. Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture).

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with the insert combination of plastic (red, hard, oil and grease resistant) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- · Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- · All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in D30mm to 60mm.

Application Areas

Versatile use, assembly and repair work, maintenance work, sheet-metal forming, prefabricated house construction, carpenter's work, scaffold construction, tent construction

Material

Handle

• Fibreglass with rubber grip

insert 1

- Plastic, red
- hard
- · Oil and grease resistant
- Universal

insert 2

- · Nylon, white
- hard
- Very wear-resistant
- no chipping (even at tempeatures below
- zero)

 Oil and grease resistant

Housina

· Reinforced cast iron, black

Order information

ø	i ‡	Din —	nensions Length x Width x Height	Ĭ.	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
[mm]				[g]				
30	90	300	300 x 90 x 34	451	4030618306337	AAA905c002	21-04-09-16	3768.030
40	115	325	325 x 115 x 40	875	4030618306344	AAA905c002	21-04-09-16	3768.040
50	135	335	335 x 135 x 50	1235	4030618306351	AAA905c002	21-04-09-16	3768.050
60	150	410	410 x 150 x 60	1805	4030618306368	AAA905c002	21-04-09-16	3768.060

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.