

ヒンジ・ロングタイプ

25165.0045



製品説明

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

材質


本体

- ステンレス鋼 1.4301 (SUS304相当)

軸

- ステンレス鋼 1.4301 (SUS304相当)


寸法図




picture 1

picture 2

picture 3



発注情報

b ₁	l ₁	寸法			保持力			 [g]	製品番号
		d ₂ [mm]	h ₁ 約	h ₂	F ₁ 約	F ₂ 約 [N]	F ₃ 約		
without bores – 図 1, ステンレス鋼									
50	75	6	10	2	2500	2250	1300	93	25165.0045

法令(コンプライアンス)

RoHS準拠

2011/65/EUと2015/863指令に適合しています

SVHC材の含有は無し

0.1%(質量%濃度)以上の高懸念物質(SVHC)は使用していません-2024年1月23日SVHCリスト対象.

プロポジション65の物質は含有していません

プロポジション65の指定物質は含まれていません

<https://www.P65Warnings.ca.gov/>

紛争物質は使用していません

本製品は、コンゴ民主共和国や隣国地域から産出されるチタン、錫、金、タングステンなどのいかなる「紛争鉱物」に由来する物質を使っていません。