

## SIMPLEXソフトハンマー、 Φ50(取付け部Φ40)・TPEソフト/ゴム複合材； 鑄鉄製ハウジング と高品質木製ハンドル付

3013.051



### 製品説明

This SIMPLEX soft-face mallet comes with special D50mm inserts that are built into the D40mm housing. The oversized contact surfaces provide maximum protection during the gentle processing of workpieces with sensitive surfaces. This model is available with the insert combination of TPE-soft / TPE-mid.

The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

The grey, medium hard TPE-mid insert (series 3203) allows for a more powerful impact force that is comparable to that of the rubber composition insert (series 3202).

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

This translates to savings in both money and resources.

Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, non-marring) / TPE-mid (grey, medium hard, non-marring).
- Oversized D50mm contact surfaces are built into the D40mm housing: maximum protection during work on sensitive surfaces.
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.

### 応用分野

Window and door construction, placing fragile tiles, floor tiling, positioning and adjusting of light/delicate workpieces, joiner's work, furniture assembly, parquet and laminate flooring

### 材質

#### ハンドル

- 木製

#### インサート 1

- TPEソフト、青
- 打痕が付きにくい
- ソフト

#### インサート 2

- TPEミディアムグレー
- 打痕が付きにくい
- 中硬

#### ハウジング

- 可鍛鑄鉄

### 発注情報

Ø	長さ	幅	高さ	長さ x 幅 x 高さ	重量	GTIN	proficl@ss 5.0	ecl@ss 10.1	製品番号 <sup>1)</sup>
[mm]	[mm]	[mm]	[mm]	[mm]	[g]				
50	110	330		330 x 120 x 50	1070	4030618313946	AAA905c002	21-04-09-16	3013.051

<sup>1)</sup> このハンマーでは径40用のハウジングに特別な径50のインサートを組合わせています。

## 法令(コンプライアンス)

### RoHS準拠

2011/65/EUと2015/863指令に適合しています

### SVHC材の含有は無し

0.1%(質量%濃度)以上の高懸念物質(SVHC)は使用していません-2024年6月27日SVHCリスト対象.

### プロポジション65の物質は含有していません

プロポジション65の指定物質は含まれていません

<https://www.P65Warnings.ca.gov/>

### 紛争物質は使用していません

本製品は、コンゴ民主共和国や隣国地域から産出されるチタン、錫、金、タングステンなどのいかなる「紛争鉱物」に由来する物質を使っていません.