

Scharnieren • elongated on both sides

25165.0050



Productbeschrijving

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

Materiaal



Huls

- RVS 1.4301

As

- RVS 1.4301


Tekening



picture 1

picture 2

picture 3



Bestelinformatie

b ₁	l ₁	Afmetingen			h ₂	F ₁ ~	Klemkracht		[g]	Artikelnr.
		d ₂ [mm]	h ₁ ~	F ₂ ~ [N]			F ₃ ~			
without bores – Afbeelding 1, Roestvast staal										
60	30	3	6	1,5	700	500	450	25	25165.0050	

Voldoet

Conform RoHS

Voldoet aan Richtlijn 2011/65/EU en richtlijn 2015/863

Bevat geen SVHC stoffen

Bevat geen SVHC-stoffen met meer dan 0,1% w/w - SVHC-lijst per 23.01.2024.

Bevat geen propositie 65 stoffen

Geen propositie 65 stoffen inbegrepen

<https://www.P65Warnings.ca.gov/>

Vrij van conflictmineralen

Dit product bevat geen stoffen die worden aangeduid als "conflictmineralen" zoals tantaal, tin, goud of wolfram uit de Democratische Republiek Congo of aangrenzende landen."