


## Scharnieren • elongated on one side

25165.1055



### Productbeschrijving

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

### Materiaal


#### Huls

- staal, verzinkt door galvanisatie, gepassiveerd


#### As

- RVS 1.4301


### Tekening



picture 1    picture 2    picture 3



## Bestelinformatie

b <sub>1</sub>	l <sub>1</sub>	b <sub>2</sub>	Afmetingen						Klemkracht				Artikelnr.	
			b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub> ~	h <sub>2</sub>	l <sub>2</sub>	F <sub>1</sub> ~	F <sub>2</sub> ~ [N]	F <sub>3</sub> ~			
[mm]													[g]	
<b>with bores – Afbeelding 2, Staal</b>														
60	40	32,5	12,5	4,2	4	8	2	25	1200	1000	1000	45	25165.1055	

## Voldoet

**Conform RoHS**

Voldoet aan Richtlijn 2011/65/EU en richtlijn 2015/863

**Bevat geen SVHC stoffen**

Bevat geen SVHC-stoffen met meer dan 0,1% w/w - SVHC-lijst per 23.01.2024.

**Bevat geen propositie 65 stoffen**

Geen propositie 65 stoffen inbegrepen

<https://www.P65Warnings.ca.gov/>

**Vrij van conflictmineralen**

Dit product bevat geen stoffen die worden aangeduid als "conflictmineralen" zoals tantaal, tin, goud of wolfram uit de Democratische Republiek Congo of aangrenzende landen."