

Płaskie śruby radełkowane • DIN 653

24770.0178



Opis produktu

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

Śruby radełkowane wykonane są z jednego elementu, z gwintem do 1ba (oznaczenie DIN: A).

Materiał

- Stal oksydowana, jakość 5.8

Więcej informacji


Uwagi

Skok i głębokość radełkowania mogą różnić się od DIN.

Inne produkty

- Śruby wysokie radełkowane, DIN 464

Rysunek



Informacje do zamówienia

d ₁	Wymiary		d ₂	k	[g]	Nr art.
	l	[mm]				
Stal						
M10	35		36	8	78	24770.0178

Zgodność

Zgodny z RoHS

Zawiera ołów - zgodny z wyjątkami 6a /6b /6c

Zawiera substancje SVHC > 0,1% mas.

Zawiera ołów – lista SVHC [REACH] z dnia 27.06.2024.

Zawiera substancje z Propozycja 65



Kontakt z ołowiem może powodować raka i bezpłodność
<https://www.P65Warnings.ca.gov/>

Wolny od minerałów konfliktu

Ten produkt nie zawiera żadnych substancji oznaczonych jako „minerały konfliktu”, takich jak tantal, cyna, złoto lub wolfram z Demokratycznej Republiki Konga lub krajów sąsiednich.