

Płaskie śruby radełkowane • DIN 653

24770.0498



Opis produktu

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

Śruby radełkowane wykonane są z jednego elementu, z gwintem do 1ba (oznaczenie DIN: A).

Materiał

- Stalowe, cynkowane galwanicznie, jakość 5.8

Więcej informacji


Uwagi

Skok i głębokość radełkowania mogą różnić się od DIN.

Inne produkty

- Śruby wysokie radełkowane, DIN 464

Rysunek



Informacje do zamówienia

Wymiary		[mm]	[g]	Nr art.
d ₁	l			
Stal				
M4	20	16	3,5	7
				24770.0498

Zgodność

Zgodny z RoHS

Zgodny zgodnie z Dyrektywą 2011/65/UE i Dyrektywą 2015/863

Nie zawiera substancji SVHC

Brak substancji SVHC o zawartości powyżej 0,1% mas. – lista SVHC z 27.06.2024.

Nie zawiera substancji Propozycji 65

Nie zawiera substancji z rozporządzenia Proposition 65.

<https://www.P65Warnings.ca.gov/>

Wolny od minerałów konfliktu

Ten produkt nie zawiera żadnych substancji oznaczonych jako „minerały konfliktu”, takich jak tantal, cyna, złoto lub wolfram z Demokratycznej Republiki Konga lub krajów sąsiednich.