

## Płaskie śruby radełkowane • DIN 653

24770.0574



## Opis produktu

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

Śruby radełkowane wykonane są z jednego elementu, z gwintem do lba (oznaczenie DIN: A).

## Materiał

- Stalowe, cynkowane galwanicznie, jakość 5.8

## Więcej informacji


## Uwagi

Skok i głębokość radełkowania mogą różnić się od DIN.

## Inne produkty

- Śruby wysokie radełkowane, DIN 464

## Rysunek



## Informacje do zamówienia

d <sub>1</sub>	Wymiary			[g]	Nr art.
	l	d <sub>2</sub>	k		
[mm]					
Stal					
M10	25	36	8	74	24770.0574

## Zgodność

## Zgodny z RoHS

Zgodny zgodnie z Dyrektywą 2011/65/UE i Dyrektywą 2015/863

## Nie zawiera substancji SVHC

Brak substancji SVHC o zawartości powyżej 0,1% mas. – lista SVHC z 27.06.2024.

## Nie zawiera substancji Propozycji 65

Nie zawiera substancji z rozporządzenia Proposition 65.

<https://www.P65Warnings.ca.gov/>

## Wolny od minerałów konfliktu

Ten produkt nie zawiera żadnych substancji oznaczonych jako „minerały konfliktu”, takich jak tantal, cyna, złoto lub wolfram z Demokratycznej Republiki Konga lub krajów sąsiednich.