

Zawiasy
25165.0225



Opis produktu

The different versions cover many applications that require a low load. These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

Material


Korpus

- Stal nierdzewna 1.4301


Oś

- Stal nierdzewna 1.4301

Rysunek



picture 1 picture 2 picture 3



Informacje do zamówienia

b ₁	l ₁	b ₂	Wymiary						Siła trzymania			[g]	Nr art.	
			d ₁	d ₂	d ₃	h ₁	h ₂	l ₂	F ₁	F ₂	F ₃			
[mm]									~	~	~			
with bores for countersunk screws – rysunek 3, Stal nierdzewna									[N]	[N]	[N]			
40	40	25	4	5	8,3	8	2	25	2000	1000	1000	33	25165.0225	

Zgodność

Zgodny z RoHS

Zgodny zgodnie z Dyrektywą 2011/65/UE i Dyrektywą 2015/863

Nie zawiera substancji SVHC

Brak substancji SVHC o zawartości powyżej 0,1% mas. – lista SVHC z 23.01.2024.

Nie zawiera substancji Propozycji 65

Nie zawiera substancji z rozporządzenia Proposition 65.

<https://www.P65Warnings.ca.gov/>

Wolny od minerałów konfliktu

Ten produkt nie zawiera żadnych substancji oznaczonych jako „minerały konfliktu”, takich jak tantal, cyna, złoto lub wolfram z Demokratycznej Republiki Konga lub krajów sąsiednich.