

Drop-mallets/Punches kit · 4 pcs.

3408s005



Opis produktu

These little helpers made by Halder are packaged in a 4 pcs. box set. The high-quality plastic case ensures that the products are easy to store and carry along. The punches and drop-mallets are fitted on both ends with replaceable, very wear-resistant and splinter-proof heads made of special nylon (art. no. 3508.010 / .015 / .020 / .030). They thus allow for secure and gentle work with a steel hammer.

Besides, drop-mallets are, in effect, soft-face mallets without a handle, allowing the user to hold the hammer head directly in the hand. Suitable for use in situations where limited accessibility makes it impossible to work with a mallet, they are also ideal for applying exactly the amount of impact force that is needed for striking the workpiece with perfect precision and for working with minimum force. The drop-mallets offer non-rebound comfort thanks to their steel shot filling. The resulting effect is that the energy of the steel shot is transferred with a slight delay when the mallet's contact surface hits the workpiece. The reduced rebound lets the impact energy be absorbed with perfect efficiency, allowing for work with reduced strain on the joints and low noise. The drop-mallets make work much less strenuous - especially in environments with limited accessibility, e.g. during assembly, repair and maintenance, and during work that calls for a well-dosed application of impact force.

Product features:

- 4 pcs. bonus box set consisting of two drop-mallets and two punches.
- Premium, long-lasting plastic case for easy carrying.
- Punches with diameters of 10mm and 15mm (art. no. 3408.010 / 3408.015).
- Drop-mallets with diameters of 20 mm and 30 mm (art. no. 3408.020 / 3408.030).
- Replaceable, very wear-resistant and splinter-proof heads made of special nylon fitted on both ends.
- Allow for secure, gentle and noise-dampening work with a steel hammer.
- The drop-mallets are also non-rebound.
- Allow for an exact application of the impact force.
- The solution for work in areas with limited accessibility.

Material

Wkładki


- Nylon, biały
- twardy
- Bardzo odporny na ścieranie
- nie łuszczy się (nawet w ujemnych temp.)
- Odporny na działanie oleju i smarów

Więcej informacji

Inne produkty

- Pobijaki, bezodrzutowe
- Przebijaki

Informacje do zamówienia

Wymiary Długość x Szerokość x Wysokość [mm]	 [g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Nr art.
230 x 45 x 180	1220	4030618312109	AAA905c002	21-04-09-16	3408s005

Zgodność

Zgodny z RoHS

Zawiera ołów - zgodny z wyjątkami 6a /6b /6c

Zawiera substancje SVHC > 0,1% mas.

Zawiera ołów – lista SVHC [REACH] z dnia 27.06.2024.

Zawiera substancje z Propozycja 65



Kontakt z ołowiem może powodować raka i bezpłodność
<https://www.P65Warnings.ca.gov/>

Wolny od minerałów konfliktu

Ten produkt nie zawiera żadnych substancji oznaczonych jako „minerały konfliktu”, takich jak tantal, cyna, złoto lub wolfram z Demokratycznej Republiki Konga lub krajów sąsiednich.