

**Gångjärn • elongated on one side**  
25165.0155



**Produktbeskrivning**

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

**Material**


**Kropp**

- Rostfritt stål 1.4301

**Axlig**

- Rostfritt stål 1.4301


**Ritning**




picture 1

picture 2

picture 3



## Orderinformation

b <sub>1</sub>	l <sub>1</sub>	b <sub>2</sub>	Dimension						Hållkraft				Art.nr.	
			b <sub>3</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	F <sub>1</sub>	F <sub>2</sub>	F <sub>3</sub>			
			[mm]						~	~	~	[g]		
with bores – Bild 2, rostfritt stål														
60	40	32,5	12,5	4,2	4	8	2	18	1200	1000	1000	45	25165.0155	

## Överensstämmelse

## RoHS-kompatibel

Överensstämmer med direktiv 2011/65/EU och direktiv 2015/863

## Innehåller inte SVHC-ämnen

Inga SVHC-ämnen med mer än 0,1 % w/w - SVHC-lista [REACH] per 23.01.2024.

## Innehåller inte ämnen i proposition 65

Inga Proposition 65-ämnen inkluderade

<https://www.P65Warnings.ca.gov/>

## Fri från konfliktmineraler

Denna produkt innehåller inga ämnen betecknade som konfliktmineraler" såsom tantal, tenn, guld eller volfram från Demokratiska republiken Kongo eller angränsande länder."