

## SHEET METAL FORMER



### SIMPLEX SERIES 3117

- Perfect for working on delicate workpieces
- Extremely lightweight aluminium housing
- All parts are replaceable
- High quality wood handle
- 2 different inserts: TPE-soft (blue, soft, **non-marring**) / Superplastic (white, medium hard, very durable, wear-resistant)

Art. No.	∅ [mm]	[g]	[mm]
3117.030	30	185	295
3117.040	40	350	325

### MAGNETIC HOLDER



- Tremendous holding force thanks to neodymium magnets
- Ideal for holding vapour barrier to steel surfaces
- Easily hang compressed air hoses, tape rolls, cables and clothing
- Rubber-encased magnet prevents scratches and is resistant to oil

Art. No.	Colour	∅ [mm]	[g]
3688.002	blue	75	250
3688.003	black	75	250

## THE 2 IN 1 HAMMER



### FERROPLEX SERIES 3677

- Industrial/mechanics hammer and soft-face mallet in one
- With steel tube handle and ergonomic rubber grip
- Hammer head made of heat-treated steel
- Opposite side with exchangeable nylon insert, **no chipping** (even at temperatures below zero)

Art. No.	∅ [mm]	[g]	[mm]
3677.030	30	600	290
3677.035	35	800	295

### ERWIN HALDER KG

Erwin-Halder-Straße 5-9  
88480 Achstetten-Bronnen  
Germany

T +49 7392 7009-0  
F +49 7392 7009-160  
info@halder.de  
www.halder.de

Distributed by:



103.133

GB/EH/09/2020

# HALDER



german  
brand  
award  
'19  
gold



# THE ORIGINAL FOR PROFESSIONALS

## CARPENTRY / SHEET METAL FORMING

## WOOD WORKING



### SIMPLEX SERIES 3027

- All parts are replaceable
- High quality wood handle
- Robust and extremely durable cast iron housing
- 2 different inserts: Rubber composition (black, medium hard, impact cushioning, odorless, low-wear hardness) / Superplastic (white, medium hard, very durable, wear-resistant)

Art. No.	∅ [mm]	[g]	[mm]
3027.060	60	1.510	405
3027.080	80	2.770	490

### SLEDGE HAMMER SIMPLEX SERIES 3027.VS

- All parts are replaceable
- High quality Hickory handle, high density, long-stranded, very robust
- Robust and extremely durable cast iron housing
- 2 different inserts: Rubber composition (black, medium hard, impact cushioning, odorless, low-wear hardness) / Superplastic (white, medium hard, very durable, wear-resistant)

Art. No.	∅ [mm]	[g]	[mm]
3027.081	80	3.170	800
3027.100	100	5.350	1.000

## WOOD WORKING NON-REBOUND



### SECURAL MODEL 3380

- **Maximum rebound damping**
- Absolutely unbreakable connection
- Interchangeable inserts made of polyurethane: rectangular, noise-dampening, impact cushioning, wear-resistant

Art.-No.	Length x Width [mm]	[g]	[mm]
3380.040	30x40	680	300
3380.045	35x45	1.000	310

### SUPERCRAFT SERIES 3377

- **Non-rebound, high impact**
- Break-proof steel tube handle and ergonomic, anti-slip grip
- Replaceable inserts made of hard extruded nylon: **No chipping** (even at temperatures below zero), will not crack

Art. No.	∅ [mm]	[g]	[mm]
3377.050	50	1.150	315
3377.060	60	1.750	325
3377.070	70	2.250	335

## PLUMBER / SHEET METAL WORK



### SUPERCRAFT SERIES 3366

- **Non-rebound, high impact**
- Safe alternative to hitting steel on steel
- Vibration-reducing Hickory handle
- Replaceable inserts made of hard extruded nylon: **No chipping** (even at temperatures below zero), will not crack

Art. No.	∅ [mm]	[g]	[mm]
3366.020	20	245	300
3366.025	25	325	305
3366.030	30	460	330
3366.035	35	560	335
3366.040	40	715	355

### BASEPLEX SERIES 3968

- High-quality zinc die cast base body with handle impact protection
- Wooden handle ergonomic, varnished
- Replaceable inserts: Cellulose acetate (red, hard, oil and grease resistant) / Nylon (white, hard, wear-resistant, **no chipping**)

Art. No.	∅ [mm]	[g]	[mm]
3968.025	25	215	270
3968.030	30	360	280
3968.040	40	510	325