

星形把手 · DIN 6336 輕合金 EH 24660.




產品描述

這些星形夾具根據 DIN 6336 製造。


材質

把手
• 輕合金 (鋁), 未拋光或拋光


圖面





圖片 1




圖片 2



圖片 3



圖片 4



圖片 5

訂單資訊

d ₁	d ₂	d ₃ H7	d ₄	尺寸						[g]	品號
				d ₅	h ₁	h ₂	h ₃	t ₁ min	t ₂		
未加工, 型式 A – 相片 1, 未拋光											
40	14	–	–	–	26	–	13	–	–	36	24660.0040
50	18	–	–	–	34	–	17	–	–	70	24660.0050
63	20	–	–	–	42	–	21	–	–	128	24660.0063
80	25	–	–	–	52	–	25	–	–	245	24660.0080
有平滑 盲孔, 型式 C – 相片 3, 未拋光											
40	14	8	–	–	–	25	–	15	–	30	24660.0240
50	18	10	–	–	–	32	–	18	–	63	24660.0250
63	20	12	–	–	–	40	–	22	–	117	24660.0263
80	25	16	–	–	–	50	–	28	–	223	24660.0280
有母牙 螺紋, 鑽孔, 型式 D – 相片 4, 未拋光											
40	14	–	M 8	8,4	–	25	–	–	13	32	24660.0340
50	18	–	M10	10,5	–	32	–	–	16	62	24660.0350
63	20	–	M12	13,0	–	40	–	–	20	109	24660.0363
80	25	–	M16	17,0	–	50	–	–	20	218	24660.0380
有盲孔, 母牙, 型式 E – 相片 5, 未拋光											
40	14	–	M 8	–	–	25	–	15	–	33	24660.0440
50	18	–	M10	–	–	32	–	18	–	63	24660.0450
63	20	–	M12	–	–	40	–	22	–	118	24660.0463
80	25	–	M16	–	–	50	–	28	–	227	24660.0480
有平滑 盲孔, 型式 C – 相片 3, 已拋光											
40	14	8	–	–	–	25	–	15	–	30	24660.0640
50	18	10	–	–	–	32	–	18	–	63	24660.0650
63	20	12	–	–	–	40	–	22	–	117	24660.0663
80	25	16	–	–	–	50	–	28	–	223	24660.0680

d ₁	d ₂	d ₃ H7	d ₄	尺寸						[g]	品號	
				d ₅ [mm]	h ₁	h ₂	h ₃	t ₁ min	t ₂			
有母牙 螺紋，鑽孔，型式 D - 相片 4, 已拋光												
40	14	-	M 8	8,4	-	25	-	-	-	13	32	24660.0740
50	18	-	M10	10,5	-	32	-	-	-	16	62	24660.0750
63	20	-	M12	13,0	-	40	-	-	-	20	109	24660.0763
80	25	-	M16	17,0	-	50	-	-	-	20	218	24660.0780
有盲孔，母牙，型式 E - 相片 5, 已拋光												
40	14	-	M 8	-	-	25	-	15	-	-	33	24660.0840
50	18	-	M10	-	-	32	-	18	-	-	63	24660.0850
63	20	-	M12	-	-	40	-	22	-	-	118	24660.0863
80	25	-	M16	-	-	50	-	28	-	-	227	24660.0880

遵守

符合 RoHS

含鉛 - 相容除了例外 6a / 6b / 6c.

含有 >0.1% w/w 的 SVHC 物質

含鉛 - SVHC [REACH] 清單截至 2024 年 1 月 23 日

包含 65 號提案的物質



接觸鉛會導致癌症和生殖危害。接觸鎳會導致癌症。

<https://www.P65Warnings.ca.gov/>

不含衝突礦物

本產品不含來自剛果民主共和國或鄰近國家的任何被指定為“衝突礦物”的物質，例如鈹、錫、金或鎢。