

絞鏈 • elongated on both sides

EH 25165.



產品描述

The different versions cover many applications that require a low load.

These metal hinges are characterised by their simple design and the different versions:

- without bores
- with bores
- with bores for countersunk screws

The version without bores can be assembled by welding or by inserting a specific drilling pattern.

材質



本體

- 不銹鋼 1.4301
- 鋼，鍍鋅，鈍化

軸

- 不銹鋼 1.4301


圖面



picture 1

picture 2

picture 3



訂單資訊

b ₁	l ₁	b ₂	b ₃	尺寸						夾持力			[g]	品號	
				d ₁	d ₂	d ₃	h ₁ ~	h ₂	l ₂	F ₁ ~	F ₂ ~ [N]	F ₃ ~			
[mm]															
without bores – 相片 1, 不銹鋼															
60	30	–	–	–	3	–	6	1,5	–	700	500	450	25	25165.0050	
80	40	–	–	–	4	–	8	2,0	–	1200	1000	1000	59	25165.0075	
100	50	–	–	–	6	–	10	2,0	–	1200	1600	700	99	25165.0005	
120	60	–	–	–	6	–	10	2,0	–	1100	2500	1000	139	25165.0010	
with bores – 相片 2, 不銹鋼															
60	30	48	9,0	3,2	3	–	6	1,5	18	700	500	450	24	25165.0150	
80	40	65	12,5	4,2	4	–	8	2,0	25	1200	1000	1000	58	25165.0175	
100	50	80	15,0	5,2	6	–	10	2,0	30	1200	1600	700	98	25165.0105	
120	60	96	18,0	5,2	6	–	10	2,0	36	1100	2500	1000	136	25165.0110	
with bores – 相片 2, 鋼															
60	30	48	9,0	3,2	3	–	6	1,5	18	700	500	450	24	25165.1050	
80	40	65	12,5	4,2	4	–	8	2,0	25	1200	1000	1000	58	25165.1075	
100	50	80	15,0	5,2	6	–	10	2,0	30	1200	1600	700	98	25165.1005	
120	60	96	18,0	5,2	6	–	10	2,0	36	1100	2500	1000	136	25165.1010	
with bores for countersunk screws – 相片 3, 不銹鋼															
60	30	48	9,0	4,0	3	6,4	6	1,5	18	700	500	450	24	25165.0250	
80	40	65	12,5	5,0	4	8,3	8	2,0	25	1200	1000	1000	58	25165.0275	
100	50	80	15,0	5,0	6	8,3	10	2,0	30	1200	1600	700	98	25165.0205	
120	60	96	18,0	5,0	6	8,3	10	2,0	36	1100	2500	1000	136	25165.0210	
with bores for countersunk screws – 相片 3, 鋼															
60	30	48	9,0	4,0	3	6,4	6	1,5	18	700	500	450	24	25165.2050	
80	40	65	12,5	5,0	4	8,3	8	2,0	25	1200	1000	1000	58	25165.2075	
100	50	80	15,0	5,0	6	8,3	10	2,0	30	1200	1600	700	98	25165.2005	
120	60	96	18,0	5,0	6	8,3	10	2,0	36	1100	2500	1000	136	25165.2010	

遵守

符合 RoHS

符合指令 2011/65/EU 和指令 2015/863

不含 SVHC 物質

不含超過 0.1% w/w 的 SVHC 物質 - 截至 2024 年 1 月 23 日的 SVHC 清單。

不含 65 號提案物質

不包括 65 號提案物質

<https://www.P65Warnings.ca.gov/>

不含衝突礦物

本產品不含來自剛果民主共和國或鄰近國家的任何被指定為“衝突礦物”的物質，例如鈿、錫、金或鎢。