

FAQ - 分割定位柱

Which type of connection is available?

3-pin plug M8x1 (knurled screw connection freely rotatable), with PUR cable 0.5 m

Which IP protection class is available?

P 67

What is the power consumption?

≤ 8 mA

How is the switching frequency?

1,000 Hz

In what temperature range may the sensor be used?

-25 °C to +75 °C

Is there a (reverse) polarity protection?

Yes

Is there a short-circuit protection?

Yes

Is there a switch-on impulse suppression?

Yes