

Spring Plungers • with pin and internal hexagon

EH 22030.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Also available in INCH

Spring Plungers • with pin and slot

EH 22050.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Also available in INCH

Spring Plungers • with internal hexagon

EH 22060.



- Can be used for locating or for applying pressure, as a detent or for ejection

EXTENSION
SPRING LOAD

Spring Plungers • with internal hexagon and seal

EH 22060.



- Can be used for locating or for applying pressure, as a detent or for ejection
- By means of the seal, liquid cannot penetrate into the spring plunger

Spring Plungers • long

EH 22070.



- To be used for ejecting, as a detent, for applying pressure or as a shock element

Spring Plungers • smooth

EH 22070.



- Especially designed for the use in tool-making. Usable as ejection pins and spring stops

Spring Plungers • smooth, with collar and pin

EH 22080.



- To be used for locating, tightening, as an assembly support, for applying pressure, as a detent, for ejection or as a shock absorber



www.halder.com/springplungers

LATERAL SPRING PLUNGERS

Our lateral plungers are the perfect choice for all applications that require you to position and press on workpieces. The models we offer also include screw-in and press-in options as well as versions that are sealed against chips and dirt.

Our premium-grade lateral plungers are also available as imperial versions. These models are available as press-in versions.



www.halder.com/lateral-spring-plungers



EN/1000/10.23

www.halder.com

HALDER

Erwin Halder KG
Erwin-Halder-Straße 5-9
88480 Achstetten-Bronnen
Germany

T +49 7392 7009-0
F +49 7392 7009-160
info@halder.com
www.halder.com

MADE IN GERMANY.


HALDER

SPRING PLUNGERS

THE WISER HEAD GIVES IN

SPRING PLUNGERS

WITH BALL - WITH PIN OR WITH MOVEABLE BALL



PATENTED, CERTIFIED AND SECURE

Our spring plungers can be used for locating or for applying pressure, as a detent or for ejection. They are specially tested for spring range and forces and provide an outstanding functional reliability.

Apart from carrying an extensive selection of metric models we can also offer a wide range of INCH models.

Are you faced with an installation situation with specific requirements? We will find the solution! We also develop special solutions, especially for your needs - even in small batches.

OUR PRODUCT RANGE

SPRING PLUNGERS

Spring Plungers • with ball and internal hexagon

EH 22030.



- Can be used for locating or for applying pressure, as a detent or for ejection

FURTHER DIMENSIONS

Spring Plungers • with moveable ball and internal hexagon

EH 22031.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Moveable ball prevents damage

Spring Plungers • with ball and slot

EH 22050.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Also available in INCH

FURTHER DIMENSIONS

Spring Plungers • with moveable ball and slot

EH 22051.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Moveable ball prevents damage

Spring Plungers • smooth, without collar

EH 22080.



- Can be used for locating or for applying pressure, as a detent or for ejection

Spring Plungers • smooth, without collar, with moveable ball

EH 22081.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Moveable ball prevents damage

Spring Plungers • headed, with ball and internal hexagon

EH 22030.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Precise screwing depth due to head

Spring Plungers • headed, with ball and slot

EH 22050.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Precise screwing depth due to head

Spring Plungers • plastic

EH 22040.



- Can be used for locating or for applying pressure, as a detent or for ejection

Spring Plungers • with ceramic ball and slot

EH 22050.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Electrical insulation
- Stainless steel A4

Spring Plungers • with moveable ceramic ball and slot

EH 22051.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Moveable ball prevents damage
- Electrical insulation
- Stainless steel A4

NEW

Spring Plungers • smooth, with collar and ball

EH 22080.



- Can be used for locating or for applying pressure, as a detent or for ejection

FURTHER DIMENSIONS

Halter • for spring plungers

EH 22082.



- Holders are used to mount spring plungers, smooth, with collar (EH 22080.) on the side

Spring Plungers • with collar and ball, front slot

EH 22075.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Ball side mounting
- For applications that require a flat surface when screwed in

NEW

Spring Plungers • smooth, with collar and ball, self-clamping

EH 22080.



- Can be used for locating or for applying pressure, as a detent or for ejection
- Due to expanding fit of the body, the spring plungers can accommodate variation of up to 0,2 mm in the locating bore
- Also available in INCH

Spring Plungers • smooth, long, with collar and ball

EH 22080.



- Can be used for locating or for applying pressure, as a detent or for ejection

Spring Plungers • double-sided

EH 22090.



- To be used for locating and securing, as well as electric connection

Spring Bodies

EH 22100.



- Can be used for locating