

**SIMPLEX soft-face mallets** • TPE-mid / rubber composition; with cast iron housing and high-quality wooden handle  
3023.040



**Product Description**

The SIMPLEX series 3023 is available with the insert combination of TPE-mid / rubber composition. Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer. The grey TPE-mid insert (series 3203) allows for an impact force that is comparable to the black rubber insert. The difference is that it will not leave any undesired black marring. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D80mm, while the D60mm and D80mm versions are also available with rubber insert and “stand-up”. The 60mm and D80mm version is also available with an extra short handle (art. no. 3023.062 and 3023.082).

**Product features:**

- SIMPLEX soft-face mallet with the insert combination of TPE-mid (grey, medium hard, no marring) / rubber composition (black, medium hard, impact cushioning, odourless, low-wear).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm, in size D60mm and D80 mm with rubber insert and “stand-up”.
- D60mm and D80mm available with an extra short handle (art. no. 3023.062 and 3023.082)

**Application Areas**

Gardening and landscaping, paving, masonry and stairs setting, natural stone setting

**Material**

**Handle**

- Wood

**insert 1**

- TPE-mid, grey
- Non-marring
- Medium hard

**insert 2**

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- Low-wear

**Housing**

- Cast iron

**Order information**

| Ø  | Dimensions |      | Length x Width x Height | [g] | GTIN          | proficl@ss<br>5.0 | ecl@ss 10.1 | Art. No. |
|----|------------|------|-------------------------|-----|---------------|-------------------|-------------|----------|
|    | [mm]       | [mm] |                         |     |               |                   |             |          |
| 40 | 115        | 325  | 325 x 115 x 40          | 630 | 4030618304531 | AAA905c002        | 21-04-09-16 | 3023.040 |

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.