

## SIMPLEX cast iron housing

EH 3011.



### Product Description

The SIMPLEX cast iron housing (series 3011) is the most widely used housing in Halder's product selection. It comes with an integrated handle protection sleeve, protecting the handle in case of mis-strikes. Robust and damping vibrations, the housing is very durable and offers excellent break resistance - not least thanks to its wear-resistant powder coating. This housing is available for SIMPLEX soft-face mallets with sizes ranging from D30mm to D140mm. A modified version is also used in combination with SIMPLEX splitting axes and the SIMPLEX splitting maul.

Product features:

- SIMPLEX cast iron housing
- With integrated handle protection sleeve
- Excellent break resistance
- No chipping
- Vibration-dampening
- With wear-resistant powder coating
- Very durable
- Halder top seller
- Available for SIMPLEX soft-face mallets between D30mm and D140mm and as a special version for SIMPLEX splitting axes and the SIMPLEX splitting maul.

### Material

#### Housing

- Cast iron

### More information


#### Notes

Including screw, nut and spring washer.

#### Further products

- Replacement screws, SIMPLEX cast iron housing

### Order information

Ø	Dimensions	 [g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
	Length x Width x Height [mm]					
30	52 x 32 x 61	225	4030618301295	EAB585c005	21-04-92-30	<a href="#">3011.030</a>
40	62 x 43 x 76	420	4030618301301	EAB585c005	21-04-92-30	<a href="#">3011.040</a>
50	74 x 54 x 98	725	4030618301318	EAB585c005	21-04-92-30	<a href="#">3011.050</a>
60	74 x 32 x 109	975	4030618301325	EAB585c005	21-04-92-30	<a href="#">3011.060</a>
80	90 x 85 x 146	1785	4030618301332	EAB585c005	21-04-92-30	<a href="#">3011.080</a>
100	105 x 100 x 192	3550	4030618301349	EAB585c005	21-04-92-30	<a href="#">3011.100</a>
125/140	114 x 128 x 226	5370	4030618301356	EAB585c005	21-04-92-30	<a href="#">3011.125</a>

### Compliance

#### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.