

星形把手 · DIN 6336 轻合金
EH 24660.



产品描述


These star grips are manufactured according to DIN 6336.

材质


把手

- 轻合金 (铝), 未抛光或抛光


图面





图片 1




图片 2



图片 3



图片 4



图片 5

订单信息

d ₁	d ₂	d ₃ H7	d ₄	尺寸						[g]	品号
				d ₅	h ₁	h ₂	h ₃	t ₁ min	t ₂		
未加工, 型式 A – 相片 1, 未抛光											
40	14	-	-	-	26	-	13	-	-	36	24660.0040
50	18	-	-	-	34	-	17	-	-	70	24660.0050
63	20	-	-	-	42	-	21	-	-	128	24660.0063
80	25	-	-	-	52	-	25	-	-	245	24660.0080
有平滑盲孔, 型式 C – 相片 3, 未抛光											
40	14	8	-	-	-	25	-	15	-	30	24660.0240
50	18	10	-	-	-	32	-	18	-	63	24660.0250
63	20	12	-	-	-	40	-	22	-	117	24660.0263
80	25	16	-	-	-	50	-	28	-	223	24660.0280
有母牙螺纹, 钻孔, 型式 D – 相片 4, 未抛光											
40	14	-	M 8	8,4	-	25	-	-	13	32	24660.0340
50	18	-	M10	10,5	-	32	-	-	16	62	24660.0350
63	20	-	M12	13,0	-	40	-	-	20	109	24660.0363
80	25	-	M16	17,0	-	50	-	-	20	218	24660.0380
有盲孔, 母牙, 型式 E – 相片 5, 未抛光											
40	14	-	M 8	-	-	25	-	15	-	33	24660.0440
50	18	-	M10	-	-	32	-	18	-	63	24660.0450
63	20	-	M12	-	-	40	-	22	-	118	24660.0463
80	25	-	M16	-	-	50	-	28	-	227	24660.0480
有平滑盲孔, 型式 C – 相片 3, 已抛光											
40	14	8	-	-	-	25	-	15	-	30	24660.0640
50	18	10	-	-	-	32	-	18	-	63	24660.0650
63	20	12	-	-	-	40	-	22	-	117	24660.0663
80	25	16	-	-	-	50	-	28	-	223	24660.0680

d ₁	d ₂	d ₃ H7	d ₄	尺寸						[g]	品号	
				d ₅ [mm]	h ₁	h ₂	h ₃	t ₁ min	t ₂			
有母牙 螺纹, 钻孔, 型式 D – 相片 4, 已抛光												
40	14	–	M 8	8,4	–	25	–	–	–	13	32	24660.0740
50	18	–	M10	10,5	–	32	–	–	–	16	62	24660.0750
63	20	–	M12	13,0	–	40	–	–	–	20	109	24660.0763
80	25	–	M16	17,0	–	50	–	–	–	20	218	24660.0780
有盲孔, 母牙, 型式 E – 相片 5, 已抛光												
40	14	–	M 8	–	–	25	–	–	15	–	33	24660.0840
50	18	–	M10	–	–	32	–	–	18	–	63	24660.0850
63	20	–	M12	–	–	40	–	–	22	–	118	24660.0863
80	25	–	M16	–	–	50	–	–	28	–	227	24660.0880

遵守

符合 RoHS

含铅 - 符合例外 6a / 6b / 6c

含有 >0.1% w/w 的 SVHC 物质

含铅 - SVHC [REACH] 清单截至 2024 年 6 月 27 日

包含 65 号提案的物质



铅暴露会导致癌症和生殖伤害

<https://www.P65Warnings.ca.gov/>

不含冲突矿物

„本产品不含来自刚果民主共和国或邻近国家的任何被指定为“冲突矿物”的物质，例如钽、锡、金或钨。