

## SIMPLEX 软面槌，50 至 40 · TPE-soft / TPE-mid; with cast iron housing and high-quality wooden handle EH 3013.



### 产品描述

This SIMPLEX soft-face mallet comes with special D50mm inserts that are built into the D40mm housing. The oversized contact surfaces provide maximum protection during the gentle processing of workpieces with sensitive surfaces. This model is available with the insert combination of TPE-soft / TPE-mid.

The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

The grey, medium hard TPE-mid insert (series 3203) allows for a more powerful impact force that is comparable to that of the rubber composition insert (series 3202).

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, non-marring) / TPE-mid (grey, medium hard, non-marring).
- Oversized D50mm contact surfaces are built into the D40mm housing: maximum protection during work on sensitive surfaces.
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.

### 应用区域

Window and door construction, placing fragile tiles, floor tiling, positioning and adjusting of light/delicate workpieces, joiner's work, furniture assembly, parquet and laminate flooring

### 材质

#### 把手

- 木材

#### 入子 1

- TPE 软，蓝色
- 不毁损的
- 软的

#### 入子 2

- TPE 中，灰色
- 不毁损的
- 中硬

#### 外壳

- 铸铁

### 订单信息

Ø	尺寸 [mm]	长 x 宽 x 高	重量 [g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	品号 <sup>1)</sup>	
50	110	330	330 x 120 x 50	1070	4030618313946	AAA905c002	21-04-09-16	3013.051

<sup>1)</sup> 此木槌镶嵌了 Ø50 的特殊嵌件在 Ø40 的外壳中。

## 遵守

### 符合 RoHS

符合指令 2011/65/EU 和指令 2015/863

### 不含 SVHC 物质

不含超过 0.1% w/w 的 SVHC 物质 - 截至 2024 年 6 月 27 日的 SVHC 清单.

### 不含 65 号提案物质

不包括 65 号提案物质

<https://www.P65Warnings.ca.gov/>

### 不含冲突矿物

„本产品不含来自刚果民主共和国或邻近国家的任何被指定为“冲突矿物”的物质，例如钽、锡、金或钨。