Precision Index Plungers • with tapered pin 22130.0162



Product Description

Precision index plungers together with bushings are a perfect combination for quick positioning and mounting.

The precise tolerance of both, the precision index plunger and the bushing, guarantees a high repeatability of these two elements.

Material

Pin

• Case-hardened steel, case-hardened, blackened and ground

Bushing

• Case-hardened steel, case-hardened, blackened and ground

Body

• Case-hardened steel, case-hardened, blackened and ground

Ball knob

· Thermoplastic, greyish black

Assembly

For precise adjustment, the grip ball and plunger should be glued grease-free after assembly. Detailed assembly instructions can be downloaded as a PDF file under "Documents".

Operation


When using locking index plungers the knob is pulled out and turned $90^\circ\!.$


More information

Notes


Bushings must be ordered separately.

Drawing





picture 2





picture 3

Order information


| Nominal | Dimensions | | | | | | | | | | | Spring load ¹⁾ | | Ĭ | Art. No. |
|--------------------------|---------------|----------------|----------------|----|----|----------------|----------------|----------------|----------------|----------------|----------------|---------------------------|----------------|-----|------------|
| diameter | d1 | d ₂ | d ₃ | d4 | d₅ | l ₁ | l ₂ | I ₃ | I ₄ | I ₅ | I ₆ | F1 | F ₂ | | |
| [mm] | n6 min. | | | | | | | | | ~ [] | ~ N] | [9] | | | |
| with locking – picture 2 | | | | | | | | | | | | | | | |
| | 12 | 23 | 20 | 32 | M8 | 6 | 3 | 35 | 13 | 33 | 40.5 | 22 | 35 | 135 | 22130.0162 |

1) statistical average value

Accessories

| | Nominal diameter | | I | Art. No. | | | | |
|---------------------------|---------------------------|----------------|----------------|----------------|----------------|----------------|----|------------|
| | | d ₁ | d ₂ | d ₃ | l ₁ | l ₂ | _ | |
| | | +0.1 | | n6 | min. | | | |
| | [mm] | | [9] | | | | | |
| Socket for precision inde | x plungers, tapered – pic | ture 3 | | | | | | |
| 0 | 12 | 8.28 | 23 | 20 | 13 | 10.0 | 25 | 22130.0192 |

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.