Down-Thrust Clamps • swivelling, size 60

23310.0067



Product Description

Universal mechanical clamping element for fast and comfortable changing and clamping of workpieces by means of manually swivelling clamping claw.

The clamps have the following advantages:

- · Rapid manual clamping by means of clamping screw.
- Easy and rapid changing of workpieces by swinging away the clamping claw to the left or right.
 The positioning ring 23310.0360 allows infinitely variable adjustment.
- The use of positioning ring 23310.0360 allows a repeatable precise clamping. Here h₁ min. increases by at least 10 mm (stroke minus 10 mm).
- · Compact design, thus little space taken-up for clamping.
- Easy adjustment even to large clamping heights due to the height adjusting cylinders.

Material

Clamp

 Case-hardened steel, case-hardened, blackened and ground

Assembly

Down-thrust clamps can be attached in two ways:

- 1. in a T-slot, using a nut for T-slots DIN 508 (EH 23010.)
- with the set screw directly in the mounting plate of, for example, a fixture

 The cylinder must make contact over the

The cylinder must make contact over the whole surface.

More information

References

The clamping height can be increased with height adjusting cylinders EH 23310. and with spacers EH 1617. and reduced with clamping inserts.

Further products

- · Positioning Rings, for down-thrust clamp
- Wrenches
- Spacers





Erwin Halder KG

www.halder.com Page 1 of 3

Published on: 10.8.2024

Drawing






Order information

| Dimensions | | | | | | | | | | Stroke | Clampin | Tightening | I | Art. No. |
|---------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------|---------|------------|------|------------|
| d ₁ | b ₁ | b ₂ | d ₃ | h ₁ | h ₂ | h ₃ | I ₁ | l ₂ | l ₃ | | force | torque | _ | |
| | | | | | | | | | | | | max. | | |
| | [mm] | | | | | | | | | | | [Nm] | [g] | |
| with clamping screw | | | | | | | | | | | | | | |
| 60 | 60 | 24 | M16 | 95 – 135 | 123 – 163 | 24 | 99 | 69 | 53 | 40 | 15 | 70 | 3020 | 23310.0067 |

Page 2 of 3 Published on: 10.8.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 27.06.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Erwin Halder KG

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 3 of 3 Published on: 10.8.2024