Vertical Toggle Clamps • with vertical base

23330.0015



Product Description

Due to their favourable power to movement ratio and their easy action the toggle clamps are versatile applicable for a wide rang of uses.

These toggle clamps can be used in the metal working industry when drilling, welding, bending, grinding, testing and fitting as well as in the wood and plastic industry in glueing, drilling, cutting and milling jigs.

The "toggle" principle of the toggle clamp allows a large and quick opening of the clamp. If unclamped the workpieces are completely cleared for unimpeded removal. The large power transmission results maximum clamping force by low hand force. The clamps are self-arresting they remain locked, resisting the force produced when machining components.

The toggle clamps are manufactured from high quality components and are designed for continuous use.

A oil resistant ergonomic 2-component handle, with increased grip area with soft surface for high ease of use.

The quickly adjustable clamping screws are provided by a retainer.

Material

Clamp

Steel, zinc-plated by galvanization, passivated

Rivet

· Stainless steel

Handle

plastic

Clamping screw

Steel, tempered, zinc-plated by galvanization

Clamping cap

Rubber, black

More information

References

Replacement clamping screws are available as accessories in the online shop.




Erwin Halder KG

www.halder.com Page 1 of 3

Published on: 10.8.2024

Drawing



Order information

Nominal	Clamping	Dimensions										Holdi	ing	α	<u>N</u>		I	Art. No.								
size	screw									force					_											
		d ₁	b ₁	b ₂	b ₃	h₁	h ₂	h ₃	h₄ min.	h ₄ max.	h ₅	I ₁	l ₂	l ₃	I ₄	l ₅	I ₆	I ₇	I ₈	F ₁	F ₂		min.	max.		
	[mm]	[mm]									[kN]			[°C]		[g]										
5	M8 x 65	8.6	35	10	8	244	65	20	16.5	45.5	55.5	141	130	101	16	54	13	32	53	1.7	3	60°	-10	80	689	23330.0015

Page 2 of 3 Published on: 10.8.2024

Accessories

	d₂ [mm]	[9]	Art. No.							
Clamping screw (spare part of toggle clamp)										
	M 8 x 65	57	23330.9006							

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 3 of 3 Published on: 10.8.2024