

SIMPLEX soft-face mallets • Rubber composition, with "Stand-Up" / Plastic; with cast iron housing and high-quality wooden handle

3026.260



Product Description

The SIMPLEX soft-face mallet D60mm with the insert combination of rubber composition / plastic is one of Halder's top sellers and has now been given a revamp:

Boasting an ingenious shape, the rubber insert with "stand-up" (3202.260) allows the hammer to stand securely on its head and reduces the need to bend over, making it possible to work in a much more ergonomic and back-friendly manner. Ultra low-wear, impact cushioning and odourless, the proven rubber blend offers a much longer service life than a conventional rubber hammer.

The red plastic insert (series 3206) is hard and also oil and grease resistant. This insert combination covers an extensive range of applications.

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

This translates to savings in both money and resources.

This version is available in the size D60mm. Also available as a sledge hammer (3026.261).

Product features:

- Further development of Halder's top seller: The rubber insert with "stand-up" (3202.260) ensures back-friendly working and reduces the need to bend over.
- SIMPLEX soft-face mallet with the insert combination of rubber composition with "stand-up" (black, medium hard, impact cushioning, odourless, low-wear) / plastic (red, hard, oil and grease resistant).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in size D60mm and as a sledge hammer (3026.061).
- Halder top seller for a large variety of applications.

Application Areas

Assembly and repair work in the automotive and truck sector, dent removal, maintenance work, scaffold construction, tent construction, prefabricated house construction, carpenter's work

This hammer features an special insert with "Stand-Up" that was incorporated into the housing.

Material

Handle

- Wood

insert 1

- Rubber composition, black, with "Stand Up"
- Medium hard
- impact cushioning
- Odorless
- Low-wear

insert 2

- Plastic, red
- hard
- Oil and grease resistant
- Universal

Housing

- Cast iron

Order information

Ø	Dimensions		Length x Width x Height	[g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.	
									[mm]
60		150	405	405 x 150 x 60	1530	4030618311102	AAA905c002	21-04-09-16	3026.260

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.