SIMPLEX soft-face mallets • Rubber composition; with cast iron housing and high-quality extra short wooden handle

EH 3002.





Product Description

This SIMPLEX soft-face mallet comes with an extra short handle. The compact design keeps the end of the handle from hitting the ground - for instance during paving work.

The SIMPLEX series 3002 is equipped with the rubber composition insert on either side. This medium hard rubber insert (series 3202) is an absolute top seller. Ultra low-wear, impact cushioning and odourless, it offers a much longer service life than a conventional rubber hammer. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality and extra short wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

Product features:

- SIMPLEX soft-face mallet with rubber composition inserts (black, medium hard, impact cushioning, odourless, low-wear) on both sides.
- · Extra short handle, end of handle not hitting the ground.
- · Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- · All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- · D60mm and D80mm available with an extra short handle.

Application Areas

Gardening and landscaping, paving curbstone setting, masonry and stair work, fence construction, scaffold construction, tent construction, prefabricated house construction, carpenter's work, maintenance / repair work

Material

Handle

Wood

Inserts

- · Rubber composition, black
- · Medium hard
- · impact cushioning
- Odorless
- Low-wear

Housing

Cast iron

Order information

Ø	—	Dim i	ensions Length x Width x Height	Handle version	ă	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
[mm]					[g]				
60	145	280	280 x 145 x 60	extra short	1496	4030618314318	AAA905c002	21-04-09-16	3002.062
80	175	325	325 x 175 x 80	extra short	2770	4030618312857	AAA905c002	21-04-09-16	3002.082

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1

Published on: 26.9.2024