SIMPLEX soft-face mallets, 50:40 • TPE-mid; with cast iron housing and high-quality wooden handle

EH 3003.





Product Description

This SIMPLEX soft-face mallet of the 3003 series comes with special D50mm inserts that are built into the D40mm housing. The oversized contact surfaces provide maximum protection during the gentle processing of workpieces with sensitive surfaces.

This model is equipped with the grey TPE-mid insert (3203.051) on either side. This grey, medium hard insert generates an impact force that is comparable to that of the black rubber composition insert (series 3202). However, it does not leave behind any undesired black marring. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, non-marring) / TPE-mid (grey, medium hard, non-marring).
- Oversized D50mm contact surfaces are built into the D40mm housing: maximum protection during work on sensitive surfaces.
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.

Application Areas

Window and door construction, placing fragile tiles, floor tiling, positioning and adjusting of light/ delicate workpieces, joiner's work, furniture assembly, parquet and laminate flooring

Material

Handle

Wood

Inserts

- TPE-mid, grey
- Non-marring
- Medium hard

Housing

Cast iron

Order information

Ø	Dimensions □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □ □			ă	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No. ¹⁾
[mm]				[g]				
50	110	330	330 x 120 x 50	680	4030618314165	AAA905c002	21-04-09-16	3003.051

¹⁾ Special inserts Ø50 are mounted into housing Ø40 at this mallet.

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1 Published on: 14.9.2024