

## SUPERCRAFT inserts for SUPERCRAFT soft-face mallets

EH 3508.



## Product Description

The nylon inserts (series 3508) with their hardness of approx. 73 Shore D are very hard. This white polyamide inserts offer outstanding impact qualities and are guaranteed to combine maximum strength with unique durability. They consist of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, they are therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. They stand up to the high impact forces produced by non-rebound soft-face mallets. What is more, they are oil and grease resistant and are also used on SUPERCRAFT soft mallets, SUPERCRAFT sledge hammers, punches and drop-mallets.

These inserts are available in sizes ranging from D10mm to D100mm.

Product features:


- SUPERCRAFT nylon insert (polyamide).
- White.
- Hard.
- Very wear-resistant.
- No chipping even in sub-zero temperatures.
- Oil and grease resistant.
- Available in sizes of D10mm to D100mm.

## Material

## Insert

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- noise-dampening
- very high impact

## Order information

Ø	Dimensions Length x Width x Height [mm]	 [g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
20	18.0 x 20.5 x 20.5	5	4030618301875	AAA905c002	21-04-91-06	<a href="#">3508.020</a>
25	26.5 x 26.5 x 20.0	10	4030618301882	AAA905c002	21-04-91-06	<a href="#">3508.025</a>
30	31.5 x 31.5 x 22.0	17	4030618301899	AAA905c002	21-04-91-06	<a href="#">3508.030</a>
35	36.5 x 36.5 x 22.0	23	4030618301905	AAA905c002	21-04-91-06	<a href="#">3508.035</a>
40	41.5 x 41.5 x 24.0	33	4030618301912	AAA905c002	21-04-91-06	<a href="#">3508.040</a>
45	45.0 x 45.0 x 26.0	43	4030618301929	AAA905c002	21-04-91-06	<a href="#">3508.045</a>
50	50.0 x 50.0 x 27.0	55	4030618301936	AAA905c002	21-04-91-06	<a href="#">3508.050</a>
60	60.0 x 60.0 x 32.0	95	4030618301943	AAA905c002	21-04-91-06	<a href="#">3508.060</a>
70	70.0 x 70.0 x 35.0	130	4030618301950	AAA905c002	21-04-09-16	<a href="#">3508.070</a>
80	81.0 x 81.0 x 37.0	195	4030618301967	AAA905c002	21-04-09-16	<a href="#">3508.080</a>

## Compliance

## RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

## Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.