Vertical Toggle Clamps • with horizontal base and safety lock



Product Description

Due to their favourable power to movement ratio and their easy action the toggle clamps are versatile applicable for a wide rang of uses.

These toggle clamps can be used in the metal working industry when drilling, welding, bending, grinding, testing and fitting as well as in the wood and plastic industry in glueing, drilling, cutting and milling jigs.

The "toggle" principle of the toggle clamp allows a large and quick opening of the clamp. If unclamped the workpieces are completely cleared for unimpeded removal. The large power transmission results maximum clamping force by low hand force. The clamps are self-arresting they remain locked, resisting the force produced when machining components.

The toggle clamps are manufactured from high quality components and are designed for continuous use.

A oil resistant ergonomic 2-component handle, with increased grip area with soft surface for high

The quickly adjustable clamping screws are provided by a retainer.

Material

Clamp

· Steel, zinc-plated by galvanization, passivated

Rivet

· Stainless steel

Handle

plastic

Clamping screw

· Steel, tempered, zinc-plated by galvanization

Clamping cap

Rubber, black

Plastic cap


PVC, black

More information

References


Replacement clamping screws are available as accessories in the online shop.


Drawing




Erwin Halder KG







23330.0604



Page 1 of 2 www.halder.com

Published on: 10.8.2024

Order information

Nominal	Clamping	Dimensions					I	Art. No.
size	screw							
		$d_1 b_1 b_2 b_3 h_1 h_2 $	h ₃ h ₄ h ₄ l ₁ l ₂ l ₃ l ₄ l ₅ l ₆ l ₇ l ₈ min. max.	F ₁ F ₂	mi	n. max.		
	[mm]		[mm]	[kN]		[°C]	[g]	
Steel								
5	M8 x 65	8.6 64 10 45 221 42.5	20 -6 22.5 141 130 101 16 54 53 13 32	2 3 7	105° -1	08 0	775	23330.0605

Accessories

	d₂ [mm]	I	Art. No.
Clamping screw (spare p		191 57	23330.9006

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024