# **SIMPLEX soft-face mallets •** Nylon; with cast iron housing and high-quality wooden handle EH 3008.





### **Product Description**

The SIMPLEX series 3008 is equipped with the nylon insert on either side.

This white insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is composed of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. Moreover, it is also oil and grease resistant.

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D80mm and as a sledge hammer (3008.081).

Product features:

- SIMPLEX soft-face mallet with nylon inserts (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant) on both sides.
- · Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm and as a sledge hammer.

#### **Application Areas**

Adjusting of workpieces, assembly of sharp-edged workpieces, housing assembly, mould construction, plant construction, hall construction, steel construction, exhibition stand construction, sheet-metal forming, repair and maintenance work

#### **Material**

#### Handle

Wood

# Inserts

- · Nylon, white
- hard
- · Very wear-resistant
- no chipping (even at tempeatures below zero)
- · Oil and grease resistant

#### Housing

Cast iron

Erwin Halder KG

# Order information

Dimensions				1	GTIN	proficl@ss	ecl@ss 10.1	Art. No.
Ø	<b> </b>	$\dashv$	Length x Width x Height	_		5.0		
[mm]				[9]				
30	90	295	295 x 90 x 30	340	4030618300229	AAA905c002	21-04-09-16	3008.030
40	115	325	325 x 115 x 40	650	4030618300236	AAA905c002	21-04-09-16	3008.040
50	135	370	370 x 135 x 50	1130	4030618300243	AAA905c002	21-04-09-16	3008.050
60	150	405	405 x 150 x 60	1500	4030618300250	AAA905c002	21-04-09-16	3008.060
80	175	490	490 x 175 x 80	2880	4030618300267	AAA905c002	21-04-09-16	3008.080



www.halder.com Page 1 of 2
Published on: 10.8.2024

# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

## **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Published on: 10.8.2024

www.halder.com Page 2 of 2