

## SIMPLEX soft-face mallets • TPE-soft / rubber composition; with cast iron housing and high-quality wooden handle EH 3012.



### Product Description

The SIMPLEX series 3012 is available with the popular insert combination of TPE-soft / rubber composition. The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring. Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance. Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt. In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D80mm and in size D60mm and D80mm with rubber insert and "stand-up" (series 3012.2). The 60mm and D80mm version is also available with an extra short handle (art. no. 3012.062 / 3012.082).

#### Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, no marring) / rubber composition (black, medium hard, impact cushioning, odourless, low-wear).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes ranging from D30mm to D80mm, in size D60mm and D80mm with rubber insert and "Stand-Up".
- D60mm and D80mm additionally available with extra short handle (art. no 3012.062 and 3012.082).

### Application Areas

Gardening and landscaping, paving, floor tiling

### Material

#### Handle

- Wood

#### insert 1

- TPE-soft, blue
- Non-marring
- Soft

#### insert 2

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless
- Low-wear

#### Housing

- Cast iron

### More information

#### Further products

- SIMPLEX soft-face mallets, Rubber composition, with "Stand-Up" / TPE-soft; with cast iron housing and high-quality wooden handle

### Order information

Ø	Dimensions		Length x Width x Height [mm]	[g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
30	90	295	295 x 90 x 30	340	4030618300564	AAA905c002	21-04-09-16	<a href="#">3012.030</a>
40	115	325	325 x 115 x 40	640	4030618300571	AAA905c002	21-04-09-16	<a href="#">3012.040</a>
50	135	370	370 x 135 x 50	1095	4030618300588	AAA905c002	21-04-09-16	<a href="#">3012.050</a>
60	150	405	405 x 150 x 60	1480	4030618300595	AAA905c002	21-04-09-16	<a href="#">3012.060</a>
80	175	490	490 x 175 x 80	2840	4030618312291	AAA905c002	21-04-09-16	<a href="#">3012.080</a>

## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.