SIMPLEX soft-face mallets • Rubber composition / nylon; with aluminium housing and high-quality wooden handle

EH 3128.





Product Description

The SIMPLEX series 3128 comes with the insert combination of rubber composition / nylon. Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer.

The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is made of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. Moreover, it is also oil and grease resistant.

The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily. It also makes the soft-face mallet a tool with minimum weight that is easy to carry along.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with the insert combination of rubber composition (black, medium hard, impact cushioning, odourless, low-wear) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily
 apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- · Available in sizes of D30mm to D60mm.

Application Areas

Folding and bending work, positioning and adjusting of light/delicate workpieces , joiner's work, furniture assembly, tinsmith work

Material

Handle

Wood

insert 1

- Rubber composition, black
- Medium hard
- · impact cushioning
- Odorless
- Low-wear

insert 2

- · Nylon, white
- hard
- Very wear-resistant
- no chipping (even at tempeatures below zero)
- · Oil and grease resistant

Housing

Erwin Halder KG

Aluminium Al

Order information

Dimensions				I	GTIN	proficl@ss	ecl@ss 10.1	Art. No.
Ø	— <u>i</u> ;		Length x Width x Height	_		5.0		
[mm]			[g]					
30	90	295	295 x 90 x 30	211	4030618305354	AAA905c002	21-04-09-16	3128.030
40	115	325	325 x 115 x 40	400	4030618305361	AAA905c002	21-04-09-16	3128.040
50	135	370	370 x 135 x 50	705	4030618305378	AAA905c002	21-04-09-16	3128.050
60	150	405	405 x 150 x 60	945	4030618305385	AAA905c002	21-04-09-16	3128.060



www.halder.com Page 1 of 2

Published on: 10.8.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Published on: 10.8.2024

www.halder.com Page 2 of 2