# **SIMPLEX soft-face mallets •** Superplastic / nylon; with aluminium housing and high-quality wooden handle

EH 3178.





## **Product Description**

The SIMPLEX series 3178 comes with the insert combination of superplastic / nylon. The superplastic insert (series 3207) is a medium hard plastic insert made of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable.

The nylon insert (series 3208) offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is composed of extruded and extremely homogeneous material and will not chip even at temperatures below zero. Moreover, it is also oil and grease resistant.

The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force. This makes it a cinch to process materials that break easily.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

This version is available in sizes ranging from D30mm to D60mm..

Product features:

- SIMPLEX soft-face mallet with the insert combination of superplastic (white, medium hard, very durable) / nylon (white, hard, very wear-resistant, no chipping even in sub-zero temperatures, oil and grease resistant).
- The extra light aluminium housing with built-in handle protection sleeve allows the user to easily apply and control the right amount of impact force (ideal of work on materials that break easily).
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- · Available in sizes of D30mm to D60mm.

## **Application Areas**

Positioning of light/delicate workpieces

#### Material

#### Handle

Wood

#### insert 1

- · Superplastic, white
- · Medium hard
- · Very durable
- · Wear-resistant

# insert 2

- · Nylon, white
- hard
- Very wear-resistant
- no chipping (even at tempeatures below
- · Oil and grease resistant

#### Housing

Erwin Halder KG

Aluminium Al

# **Order information**

Dimensions				I	GTIN	proficl@ss	ecl@ss 10.1	Art. No.
Ø	<b>─</b> <u></u>	$\rightrightarrows$	Length x Width x Height			5.0		
[mm]			[g]					
30	90	295	295 x 90 x 30	203	4030618305514	AAA905c002	21-04-09-16	3178.030
40	115	325	325 x 115 x 40	385	4030618305521	AAA905c002	21-04-09-16	3178.040
50	135	370	370 x 135 x 50	680	4030618305538	AAA905c002	21-04-09-16	3178.050
60	150	405	405 x 150 x 60	900	4030618305545	AAA905c002	21-04-09-16	3178.060



www.halder.com Page 1 of 2

Published on: 10.8.2024

# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

Published on: 10.8.2024

www.halder.com Page 2 of 2