

Młotki SIMPLEX, 50:40 • TPE-średni; z żeliwną obudową i wysokiej jakości drewnianym uchwytem EH 3003.



Opis produktu

This SIMPLEX soft-face mallet of the 3003 series comes with special D50mm inserts that are built into the D40mm housing. The oversized contact surfaces provide maximum protection during the gentle processing of workpieces with sensitive surfaces.

This model is equipped with the grey TPE-mid insert (3203.051) on either side. This grey, medium hard insert generates an impact force that is comparable to that of the black rubber composition insert (series 3202). However, it does not leave behind any undesired black marring. Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

Damping vibrations and shaped ergonomically, the high-quality wooden handle has a double coat of varnish in the grip area and is thus resistant to dirt.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted.

Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, non-marring) / TPE-mid (grey, medium hard, non-marring).
- Oversized D50mm contact surfaces are built into the D40mm housing: maximum protection during work on sensitive surfaces.
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.

Przykłady zastosowań

Budowa okien i drzwi, układanie delikatnych płytek, układanie płytek podłogowych, pozycjonowanie i regulacja lekkich / delikatnych elementów, prace stolarskie, montaż mebli, parkiet i podłogi laminowane.

Material

Uchwyt

- Drewno

Wkładki

- TPE-średni, szary
- nie brudzący
- Średnio twardy

Obudowa

- Żeliwo

Informacje do zamówienia

Ø	Wymiary	Długość x Szerokość x Wysokość [mm]	[g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Nr art. ¹⁾
							330
50	110	330					

¹⁾ Młotek został wyposażony w zestaw specjalnych końcówek 50 z jednej strony oraz 40 z drugiej.

Zgodność

Zgodny z RoHS

Zgodny zgodnie z Dyrektywą 2011/65/UE i Dyrektywą 2015/863

Nie zawiera substancji SVHC

Brak substancji SVHC o zawartości powyżej 0,1% mas. – lista SVHC z 27.06.2024.

Nie zawiera substancji Propozycji 65

Nie zawiera substancji z rozporządzenia Proposition 65.

<https://www.P65Warnings.ca.gov/>

Wolny od minerałów konfliktu

Ten produkt nie zawiera żadnych substancji oznaczonych jako „minerały konfliktu”, takich jak tantal, cyna, złoto lub wolfram z Demokratycznej Republiki Konga lub krajów sąsiednich.