

掌形把手 · DIN 6335 塑膠 EH 24730.



產品描述

材質

把手

- 熱固性塑膠 (PF 31), 黑色 (接近色號 RAL 9005)

螺絲


- 鋼, 鍍鋅
- 不鏽鋼 A2

更多資訊

注意事項


特殊製作, 例如: 不同的長度或螺桿, 材料是黃銅/不銹鋼, 歡迎洽詢。

圖面



訂單資訊

d ₁	尺寸		max. [°C]	[g]	品號
	d ₂ [mm]	l			
底部 / 側邊聯結, 鋼					
25	M 5	10	110	6,6	24730.0051
25	M 5	15	110	7,0	24730.0053
25	M 5	20	110	7,5	24730.0056
25	M 5	25	110	8,1	24730.0058
25	M 5	30	110	8,9	24730.0059
32	M 6	15	110	11,0	24730.0101
32	M 6	20	110	13,0	24730.0104
32	M 6	25	110	13,0	24730.0106
32	M 6	30	110	14,0	24730.0107
32	M 6	40	110	16,0	24730.0110
40	M 8	20	110	24,0	24730.0152
40	M 8	25	110	25,0	24730.0154
40	M 8	30	110	26,0	24730.0155
40	M 8	40	110	30,0	24730.0158
40	M 8	50	110	32,0	24730.0160
50	M10	25	110	41,0	24730.0202
50	M10	30	110	48,0	24730.0203
50	M10	40	110	51,0	24730.0206
50	M10	50	110	56,0	24730.0208
50	M10	60	110	68,0	24730.0209
63	M12	30	110	99,0	24730.0251
63	M12	40	110	93,0	24730.0254
63	M12	50	110	99,0	24730.0256
63	M12	60	110	105,0	24730.0257
63	M12	80	110	112,0	24730.0260
80	M16	40	110	198,0	24730.0302
80	M16	50	110	214,0	24730.0304
80	M16	60	110	219,0	24730.0305
80	M16	80	110	251,0	24730.0308

d ₁	尺寸		max. [°C]	 [g]	品號
	d ₂ [mm]	l			
底部 / 側邊聯結, 不銹鋼					
25	M 5	10	110	6,6	24730.1051
25	M 5	15	110	7,0	24730.1053
25	M 5	20	110	7,5	24730.1056
25	M 5	25	110	8,1	24730.1058
25	M 5	30	110	8,9	24730.1059
32	M 6	15	110	11,0	24730.1101
32	M 6	20	110	13,0	24730.1104
32	M 6	25	110	13,0	24730.1106
32	M 6	30	110	14,0	24730.1107
32	M 6	40	110	16,0	24730.1110
40	M 8	20	110	24,0	24730.1152
40	M 8	25	110	25,0	24730.1154
40	M 8	30	110	26,0	24730.1155
40	M 8	40	110	30,0	24730.1158
40	M 8	50	110	32,0	24730.1160
50	M10	25	110	41,0	24730.1202
50	M10	30	110	48,0	24730.1203
50	M10	40	110	51,0	24730.1206
50	M10	50	110	56,0	24730.1208
50	M10	60	110	68,0	24730.1209
63	M12	30	110	99,0	24730.1251
63	M12	40	110	93,0	24730.1254
63	M12	50	110	99,0	24730.1256
63	M12	60	110	105,0	24730.1257
63	M12	80	110	112,0	24730.1260
80	M16	40	110	198,0	24730.1302
80	M16	50	110	214,0	24730.1304
80	M16	60	110	219,0	24730.1305
80	M16	80	110	251,0	24730.1308

遵守

符合 RoHS

符合指令 2011/65/EU 和指令 2015/863

不含 SVHC 物質

不含超過 0.1% w/w 的 SVHC 物質 - 截至 2024 年 6 月 27 日的 SVHC 清單。

不含 65 號提案物質

不包括 65 號提案物質

<https://www.P65Warnings.ca.gov/>

不含衝突礦物

本產品不含來自剛果民主共和國或鄰近國家的任何被指定為“衝突礦物”的物質，例如鉭、錫、金或鎢。