

星型把手螺絲 · DIN 6336 塑膠 EH 24740.



產品描述

材質

把手

- DIN 7708 - 熱固性塑膠 (PF 31), 黑色 (接近色號 RAL 9005)

螺絲

- 鋼, 鍍鋅
- 不鏽鋼 A2

更多資訊

注意事項

特殊製作, 例如: 不同的長度或螺桿, 材料是黃銅/不銹鋼, 歡迎洽詢。

圖面



訂單資訊

d ₁	尺寸		max. [°C]	[g]	品號
	d ₂ [mm]	l			
底部 / 側邊聯結, 鋼					
25	M 5	10	110	7,3	24740.0051
25	M 5	15	110	7,4	24740.0053
25	M 5	20	110	8,7	24740.0056
25	M 5	25	110	8,7	24740.0058
25	M 5	30	110	9,2	24740.0059
32	M 6	15	110	14,0	24740.0101
32	M 6	20	110	15,0	24740.0104
32	M 6	25	110	14,0	24740.0106
32	M 6	30	110	16,0	24740.0107
32	M 6	40	110	17,0	24740.0110
40	M 8	20	110	28,0	24740.0152
40	M 8	25	110	31,0	24740.0154
40	M 8	30	110	32,0	24740.0155
40	M 8	40	110	35,0	24740.0158
40	M 8	50	110	38,0	24740.0160
50	M10	25	110	51,0	24740.0202
50	M10	30	110	54,0	24740.0203
50	M10	40	110	60,0	24740.0206
50	M10	50	110	64,0	24740.0208
50	M10	60	110	73,0	24740.0209
63	M12	30	110	101,0	24740.0251
63	M12	40	110	108,0	24740.0254

d ₁	尺寸		max. [°C]	[g]	品號
	d ₂ [mm]	l			
63	M12	50	110	115,0	24740.0256
63	M12	60	110	121,0	24740.0257
63	M12	80	110	143,0	24740.0260
80	M16	40	110	223,0	24740.0302
80	M16	50	110	237,0	24740.0304
80	M16	60	110	249,0	24740.0305
80	M16	80	110	274,0	24740.0308
底部 / 側邊聯結, 不銹鋼					
25	M 5	10	110	7,3	24740.1051
25	M 5	15	110	7,4	24740.1053
25	M 5	20	110	8,7	24740.1056
25	M 5	25	110	8,7	24740.1058
25	M 5	30	110	9,2	24740.1059
32	M 6	15	110	14,0	24740.1101
32	M 6	20	110	15,0	24740.1104
32	M 6	25	110	14,0	24740.1106
32	M 6	30	110	16,0	24740.1107
32	M 6	40	110	17,0	24740.1110
40	M 8	20	110	28,0	24740.1152
40	M 8	25	110	31,0	24740.1154
40	M 8	30	110	32,0	24740.1155
40	M 8	40	110	35,0	24740.1158
40	M 8	50	110	38,0	24740.1160
50	M10	25	110	51,0	24740.1202
50	M10	30	110	54,0	24740.1203
50	M10	40	110	60,0	24740.1206
50	M10	50	110	64,0	24740.1208
50	M10	60	110	73,0	24740.1209
63	M12	30	110	101,0	24740.1251
63	M12	40	110	108,0	24740.1254
63	M12	50	110	115,0	24740.1256
63	M12	60	110	121,0	24740.1257
63	M12	80	110	143,0	24740.1260
80	M16	40	110	223,0	24740.1302
80	M16	50	110	237,0	24740.1304
80	M16	60	110	249,0	24740.1305
80	M16	80	110	274,0	24740.1308

遵守

符合 RoHS

符合指令 2011/65/EU 和指令 2015/863

不含 SVHC 物質

不含超過 0.1% w/w 的 SVHC 物質 - 截至 2024 年 1 月 23 日的 SVHC 清單。

不含 65 號提案物質

不包括 65 號提案物質

<https://www.P65Warnings.ca.gov/>

不含衝突礦物

本產品不含來自剛果民主共和國或鄰近國家的任何被指定為“衝突礦物”的物質，例如鈮、錫、金或鎢。