Expander[®] Sealing Plugs • body from stainless steel EH 22880.



Product Description

Expander[®] sealing plugs are used for safe, quick and economic sealing of bore holes in fluid technology, e.g. hydraulic drilling holes in jig and fixture construction. Assembly is effected by pressing in the sealing plug into the drilling hole by means of the prescribed setting die. **Please refer to the technical data following these product information pages.**

S

Material

Body

Stainless steel 1.4305

Ball


· Roller bearing steel, heat-treated, tempered


More information

Further products

- Expander[®] Sealing Plugs, body from casehardened steel
- Expander[®] Sealing Plugs, body and ball from stainless steel
- Setting Dies, for Expander[®] sealing plug

Drawing







	-	Art. No.							
d ₁	l ₁	I ₂	d ₂	d ₃	I ₃	x	s	-	
		- ~	+0.1	max.	min.	±0.2			
	[g]								
body from	i stainless steel, b	all from steel							
3	3.6	4.6	3	2.2	3.4	0.4	1.20	0.2	22880.0053
4	4.0	5.2	4	3.3	3.8	0.2	1.50	0.4	22880.0054
5	5.5	7.0	5	4.3	5.3	0.4	2.00	0.7	22880.0055
6	6.5	8.6	6	5.3	6.3	0.4	2.50	1.3	22880.0056
7	7.5	10.1	7	6.4	7.3	0.4	3.00	1.9	22880.0057
8	8.5	11.7	8	7.4	8.3	0.3	3.50	3.2	22880.0058
9	10.0	13.7	9	8.4	9.8	0.4	4.00	4.5	22880.0059
10	11.0	15.2	10	9.4	10.8	0.4	4.50	6.1	22880.0060
12	13.0	18.0	12	10.6	12.8	0.4	5.50	9.7	22880.0062
14	15.0	20.8	14	12.7	14.5	0.4	6.35	15.0	22880.0064
16	17.0	23.7	16	14.7	16.5	0.6	7.00	22.0	22880.0066
18	19.0	26.3	18	16.7	18.5	0.6	8.00	31.0	22880.0068
20	22.0	30.5	20	18.7	21.5	0.8	9.00	46.0	22880.0070
22	25.0	34.2	22	20.7	24.5	0.8	10.00	58.0	22880.0072

d1

Application example

Working and control pressures for Expander® sealing plug, sleeve from stainless steel 1.4305											
basic material	ETG-100 AISI 1144	C15Pb 1.0403	GG-25 DIN 1691	GGG-50 DIN 1693	AlCuMg2 3.1354	AIMgSiPb 3.0615	G-AlSi7Mg 3.2371				
	p [bar]										
d ₁	450	450	450	450	450	380	380				
3-10 mm	pTest [bar]										
	1400	1400	1400	1400	1400	1200	1200				
	p [bar]										
d ₁	350	350	350	350	350	280	280				
12-22 mm	pTest [bar]										
	1150	1150	1150	1150	1150	900	900				

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.