

## Spring Plungers · smooth, with collar and pin

22080.0124



### Product Description

To be used for locating, tightening, as an assembly support, for applying pressure, as a detent, for ejection or as a shock absorber.

### Material

**Pin**  
• Thermoplastic POM, white

**Body**  
• Stainless steel 1.4303

**Spring**  
• Stainless steel

### Assembly


A tolerance of H7 is recommended for the locating hole of  $d_1$ .

### More information

### Notes

Customized design on request.  
Spring plungers are specially tested for spring range and forces.

### Drawing




### Order information

Dimensions										Stroke s	Spring load <sup>1)</sup>		Temperature		Location hole H7	Weight [g]	Art. No.
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	F <sub>1</sub>		F <sub>2</sub>	min.	max.				
+0.1 +0.04				±0.04		~	~	~		~	~						
[mm]																	
[N]																	
[°C]																	
[mm]																	
[g]																	
stainless steel body, thermoplastic pin																	
4	2.8	4.6	3.85	4	10.7	0.9	1.8	5.6	2.7	3	8.2	-30	50	4	0.5	22080.0124	

<sup>1)</sup> statistical average value

### Application example



## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.