

平压花姆指螺帽 · DIN 653

24770.0180



产品描述

Knurled thumb screws are very versatile. Three material versions for the different requirements

- steel, blackened
- steel, zinc-plated by galvanization
- stainless steel

are available.

Knurled thumb screws can be easily tightened and released by hand. The ribbed outer surface of the nut prevents slipping when tightening / releasing with the fingers.

所有滚花螺丝是整体都有螺纹的一体成型制品 (DIN-代号 A)。

材质

- 钢、染黑、品质 5.8

更多信息


注意事项

根据 DIN 规范，压花的间距和深度也不同。

更多产品

- 高压花的手转螺丝, DIN 464

图面



订单信息

d ₁	尺寸 l [mm]	d ₂	k	重量 [g]	品号
钢					
M10	40	36	8	80	24770.0180

遵守

符合 RoHS

含铅 - 符合例外 6a / 6b / 6c

含有 >0.1% w/w 的 SVHC 物质

含铅 - SVHC [REACH] 清单截至 2024 年 6 月 27 日

包含 65 号提案的物质



铅暴露会导致癌症和生殖伤害

<https://www.P65Warnings.ca.gov/>

不含冲突矿物

„本产品不含来自刚果民主共和国或邻近国家的任何被指定为“冲突矿物”的物质，例如钽、锡、金或钨。